


# EuropacPRO Cover Plate, Universal



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be used is non-standard boards will be assembled into the subrack.

## CARACTERÍSTICAS

Shielding is provided by optional EMC stainless steel gaskets, between cover plate and side panel

For variable positioning of horizontal rails e.g. for PCBs with non-standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

|                             |             |
|-----------------------------|-------------|
| <b>Acabamento:</b>          | Passivated  |
| <b>Material:</b>            | Aluminio    |
| <b>Família de produtos:</b> | EuropacPRO  |
| <b>Product Type:</b>        | Cover Plate |
| <b>Tipo:</b>                | Universal   |
| <b>Works With:</b>          | Subracks    |



## ESPECIFICAÇÕES

| Número de catálogo | Rack Width | Profundidade | Quantidade por embalagem | Unidade de embalagem |
|--------------------|------------|--------------|--------------------------|----------------------|
| 24560-031          | 42HP       | 175mm        | 2                        | Pair                 |
| 24560-032          | 42HP       | 235mm        | 2                        | Pair                 |
| 24560-033          | 42HP       | 295mm        | 2                        | Pair                 |
| 24560-041          | 63HP       | 175mm        | 2                        | Pair                 |
| 24560-042          | 63HP       | 235mm        | 2                        | Pair                 |
| 24560-043          | 63HP       | 295mm        | 2                        | Pair                 |
| 24560-051          | 84HP       | 175mm        | 2                        | Pair                 |
| 24560-052          | 84HP       | 235mm        | 2                        | Pair                 |
| 24560-053          | 84HP       | 295mm        | 2                        | Pair                 |
| 24560-054          | 84HP       | 355mm        | 2                        | Pair                 |
| 24560-055          | 84HP       | 415mm        | 2                        | Pair                 |
| 24560-056          | 84HP       | 475mm        | 2                        | Pair                 |

DETALHES ADICIONAIS DO PRODUTO

In addition, 4 contact strips per subrack are required to affix cover to horizontal rail.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

