


# Panhead Screw, Torx with Grounding



Good compromise between profile height and bearing area. Better load distribution than round heads.  
Compatible with automated assembly.

## CARACTERÍSTICAS

For fixing Horizonrail rails or chassis plate and covers onto Side panel, with GND/ Earthing function

Torx imprint bears greater torque

The star-shaped head prevents cam-out

|                             |                      |
|-----------------------------|----------------------|
| <b>Acabamento:</b>          | Chapa de Aço Zincada |
| <b>Material:</b>            | Aço                  |
| <b>Família de produtos:</b> | EuropacPRO           |
| <b>Product Type:</b>        | Screw                |
| <b>Tipo:</b>                | Panhead Screw        |



## ESPECIFICAÇÕES

| Número de catálogo | Length | Quantidade por embalagem | Tamanho da rosca | Works With | Comprimento da rosca | Torque |
|--------------------|--------|--------------------------|------------------|------------|----------------------|--------|
| 24560-130          | 14mm   | 100                      | M4               | Subracks   | 14mm                 | 1.2N·m |
| 24560-131          | 14mm   | 10                       | M4               | Subracks   | 14mm                 | 1.2N·m |
| 24560-151          | 6mm    | 100                      | M4               | Subracks   | 6mm                  | 1.2N·m |
| 24560-155          | 10mm   | 100                      | M4               | Subracks   | 10mm                 | 1.2N·m |

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.