

4G24H Twist Clip with 90° Plain Hole



CARACTERISTICI

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from T-Grid

Fast, easy and secure twist-on installation

Designed to reduce scratching of T-grid


No tools required for installation

Material: Spring Steel



SPECIFICAȚII

Număr de catalog	Article Number	Finish	Color	Hole Size (HS)	Flange Thickness (FT)	T-Grid Size	Static Load
4G24H	170490	nVent CADDY Armour	Gray	5.8 mm	1.5 mm Max	24mm	180N
4G24HWH	170500	Painted	White	5.8 mm	1.5 mm Max	24mm	180N
4G24HWHSP25	172280	Painted	White	5.8 mm	1.5 mm Max	24mm	180N



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

