


Bolt Expansion Anchor, Non-Cracked Concrete

CARACTERISTICI

Heavy duty wedge anchor

For non-cracked concrete




Material: Oțel
Finish: Electrogalvanized



SPECIFICAȚII

Număr de catalog	Article Number	Thread Size (TS)	Length (L)	Embedment Depth	A	Drill Bit Diameter
CAH08060	402602	M8	60mm	47 mm	3 mm	8mm
CAH10070	402607	M10	70mm	60 mm	3 mm	10mm

Characteristic Axial Loads from ETA-05/0242		
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25
CAH08060	-	4.8 kN
CAH10070	-	6.4 kN



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

