


Cantilever Arm with E2 Channel

CARACTERISTICI

Perforated, cold rolled

Slotted backplate



Material: Oțel
Finish: Electrogalvanized




SPECIFICAȚII

Număr de catalog	Article Number	Length (L)
CE224H0200EG	597500	200mm
CE224H0300EG	597510	300mm

Height (H): 120 mm
Width (W): 40 mm
Thickness (T): 2.4 mm
A: 20 mm
B: 34 mm
C: 15.5 mm
D: 50 mm
E: 4 mm
X: 11 x 18 mm
Y: 11 x 27 mm
Hole Size (HS): 5 mm

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

