

38 Offset Steel Eye Socket Rod Hanger, M10 Rod



NUMĂR DE CATALOG

038M0010EG

CARACTERISTICI

Structural attachment used to join hanger rod to a structure

Provides full vertical rod adjustment



ATRIBUTE PRODUS

Article Number: 598290

Material: Oțel

Finish: Electrogalvanized

Rod Size (RS): M10

Pipe Size: 100" Max

Hole Size 1 (HS1): 13 mm

Hole Size 2 (HS2): 6.7 mm

Height (H): 85 mm

Width (W): 29 mm

C: 30.6 mm

D: 19 mm



Static Load: 1112N

DETALII SUPLIMENTARE DESPRE PRODUS

Load rating dependent on wood structure strength.

For 3/8" rod through 2" pipe, use two Model #43 Wood Drive Screws. For 3/8" rod through 4" pipe, use one Model #42 1/2" x 3" Lag Screw.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

