

108 Two Hole Strap for CPVC Pipe, 1 1/2" Pipe, 40 DN, 48.3 mm OD

NUMĂR DE CATALOG

1080150EG

CARACTERISTICI

Includes flared edges to protect piping

Rated for use with CPVC fire sprinkler pipe

Includes mounting screws



ATRIBUTE PRODUS

Article Number: 597825

Material: Oțel

Finish: Pregalvanized

Pipe Size: 1 1/2"

NB/DN: 40

Outer Diameter (OD): 48.3 mm



Hole Size (HS): 5.8 mm

A: 112.7 mm

B: 87.3 mm

C: 30.2 mm

Hanger Spacing: 2.1 m Max



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

