

Push In Conduit to Conduit Clamp, 22–30 mm OD1, 22–30 mm OD2

NUMĂR DE CATALOG

12P12P

CARACTERISTICI

Ideal as spacer between same or different size conduit

No tools required for installation

Top conduit to be used for support only, not a raceway



ATTRIBUTE PRODUS

Article Number: 171250


Material: Spring Steel

Finish: nVent CADDY Armour

Outer Diameter 1 (OD1): 22 - 30 mm

Outer Diameter 2 (OD2): 22 - 30 mm

Ultimate Static Load (F): 110N



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

