

C-EC Cable to Strut Clamp, 8–12 mm OD

NUMĂR DE CATALOG

C12EC

CARACTERISTICI

One-piece cable/conduit clamp with protective boot

No screws or bolts to drop

Requires only a screwdriver or nutdriver for installation

Fits into open side of strut channel



ATRIBUTE PRODUS

Article Number: 337600

Material: Oțel

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 8 - 12 mm

Width (W): 20 mm

Thickness (T): 1.5 mm




Torque (TQ): 2 N·m

A: 18 mm Min

B: 10 mm Max

DETALII SUPLIMENTARE DESPRE PRODUS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

