

C-ES Cable to Vertical Flange Clamp, 6–12 mm OD



NUMĂR DE CATALOG

C12ES

CARACTERISTICI

Supports single run of cable

Attaches to beam flanges, angle iron, joists and other structural supports

ATTRIBUTE PRODUS

Article Number: 337000

Material: Oțel

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 6 - 12 mm

A: 43 mm

Torque (TQ): 2 N·m

DETALII SUPLIMENTARE DESPRE PRODUS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

