

C-EU Single Cable to Flange Clamp, 8–12 mm OD, 12 mm Max Flange, 41 mm Max



NUMĂR DE CATALOG

C12EU

CARACTERISTICI

Supports single run of conduit

Attaches to beam flanges, angle iron, joists and other structural supports

ATRIBUTE PRODUS

Article Number: 337300

Material: Oțel

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 8 - 12 mm



Flange Thickness (FT): 12 mm Max

A: 41 mm Max

Torque (TQ): 2 N·m

DETALII SUPLIMENTARE DESPRE PRODUS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

