

# C-EU Single Cable to Flange Clamp, 12–16 mm OD, 12 mm Max Flange, 46 mm Max



## NUMĂR DE CATALOG

**C16EU**

## CARACTERISTICI

Supports single run of conduit

Attaches to beam flanges, angle iron, joists and other structural supports

## ATTRIBUTE PRODUS

Article Number: 337310

Material: Oțel

Finish: Hot-Dip Galvanized

Outer Diameter (OD): 12 - 16 mm



Flange Thickness (FT): 12 mm Max

A: 46 mm Max

Torque (TQ): 2 N·m

## DETALII SUPLIMENTARE DESPRE PRODUS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

