

Cat HP J-Hook Mod Clip for M4-M12 Threaded Rod, 4,8 - 6,4mm Wire

NUMĂR DE CATALOG

CATHPM4Z34




Improved nVent CADDY Cat HP Mod Clip J-Hook with Rod/Wire Clip allows for quick attachment to threaded rod or wire without screws or special tools. Enjoy enhanced stability and customization for efficient cable management while gaining ultimate flexibility on the job and minimizing inventory impact.

CARACTERISTICI

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY



ATRIBUTE PRODUS

Article Number: 186082


Finish: nVent CADDY Armour

Material: Spring Steel

Rod Size (RS): M4;M6;M8;M10;M12

Wire Size: 4.8 - 6.4 mm

Static Load: 130N



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

