

Internal Strut Beam Clamp

NUMĂR DE CATALOG

INC8

CARACTERISTICI

Mounts strut within beams



ATTRIBUTE PRODUS

Article Number: 336290

Material: Spring Steel

Finish: nVent CADDY Armour

Strut Type: A (41 x 41 mm);C (21 x 41 mm)

A: 13 mm

Screw Diameter (Sc): 8



Screw Length (L): 25mm

Torque (TQ): 6 N·m

Static Load: 450N

DETALII SUPLIMENTARE DESPRE PRODUS

Strut channel must be cut 3/4" (20mm) shorter than the inner distance between the two beam flanges in order to accommodate the clamps.



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

