

Rod to C Purlin Clip, Spring Steel, M10 Hole, Threaded, 1.5–4 mm Flange

NUMĂR DE CATALOG

J1M10TI

CARACTERISTICI

Attaches to joists and C purlin

Supports threaded rod

Threaded rod hanger can swivel to provide a vertical dropdown



ATTRIBUTE PRODUS

Article Number: 175050

Material: Spring Steel

Finish: nVent CADDY Armour


Hole Size (HS): 10 mm

Hole Type: Threaded

Flange Thickness (FT): 1.5 - 4 mm

A: 10 mm Min

Static Load: 700N



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

