

Rooftop Pyramid Equipment Support Kit, 6 Post Base, 2172 mm

NUMĂR DE CATALOG

PEK6B

CARACTERISTICI

Kit includes post-base assemblies, frame and equipment-support clamps


Assembles and adjusts to size and height in minutes by one person with one tool

Innovative crossbar and equipment-support clamps enable quick assembly

Integral foam pad provides gentle interface for all roof types

Hot-dip galvanized and UV stabilized for long lasting performance

Assembled support can be lifted as one unit and easily relocated



ATRIBUTE PRODUS

Article Number: 360427

Material: Oțel; Polypropylene; Polietilenă

Finish: Hot-Dip Galvanized

Temperature: -34 to 54.4 °C

Height (H): 305 - 457 mm

Length (L): 2172mm

Post Base (A): 314 mm x 6 pc

Square Tube (B): 1981 mm x 2 pc

Cross Bar Assembly (C): 1232 mm x 4 pc

Width (W): 1588 mm

Surface Area: 0.56m²

Unit Weight: 56 kg



Ultimate Static Load (F): 9960N

Static Load Safety Factor: 3:1

DETALII SUPLIMENTARE DESPRE PRODUS

Static load must be stable and uniformly distributed across frame.

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

