

nVent CADDY Pyramid Tool-Free Pipe Clamp, 12.7–22.4 mm OD



NUMĂR DE CATALOG

PTF1C

CARACTERISTICI

Push-in clamps install without the need for additional tools or strut clamps

Clamps come in two different sizes to fit project needs

Plastic clamps and base will not corrode pipe

ATRIBUTE PRODUS

Article Number: 360484

Material: Nylon

Temperature: -45 to 65 °C

Outer Diameter (OD): 12.7 - 22.4 mm

Length (L): 40.6mm

Width (W): 19.1 mm

A: 9.5 mm

Unit Weight: 0.01 kg



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

