

Strut to Strut Connector



NUMĂR DE CATALOG

STS

CARACTERISTICI

Consists of two half castings, nut and bolt

Allows for bolting two strut channels back to back through the slots

ATRIBUTE PRODUS

Article Number: 315450

Material: Oțel

Finish: Electrogalvanized

A: 32 mm

B: 25 mm

C: 12.7 mm


Torque (TQ): 7 N·m

Static Load: 4900N

DETALII SUPLIMENTARE DESPRE PRODUS

Minimum of 2 required. Maximum spacing 1 foot (300mm).

Minimum half-slot dimensions 9/16" x 7/8" (14.3 mm x 22.2 mm).



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

