

USC Universal Strut Clamp for Pipe/Conduit, EG, 20.5–21.4 mm OD, 1/2" Pipe, 15 DN

NUMĂR DE CATALOG

USC021EG

CARACTERISTICI

Consists of two clamps, nut and bolt

Fits into open side of strut channel

Conforms with Manufacturers Standardization Society (MSS) SP-58 (Type 59)



ATTRIBUTE PRODUS

Article Number: 712045

Material: Oțel

Finish: Electrogalvanized

Outer Diameter (OD): 20.5 - 21.4 mm



Pipe Size: 1/2"

NB/DN: 15

Width (W): 32 mm

Thickness (T): 1.5 mm

Static Load: 2000N



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

