

Internal Strut Beam Clamp with Bolt, Steel, HD, EG, M10 Screw



NUMĂR DE CATALOG

ZT606HDEG

CARACTERISTICI

U-shaped clip for clamping the back of strut channel to a beam

Hex bolt included

Requires installation in pairs

ATTRIBUTE PRODUS

Article Number: 313270

Material: Oțel

Finish: Hot-Dip Galvanized;Electrogalvanized

Flange Thickness (FT): 28 mm Max

Width (W): 30 mm


Screw Diameter (Sc): 10

Static Load: 2900N

DETALII SUPLIMENTARE DESPRE PRODUS

Static Load is based on one pair of Strut Beam Clamps.

Include strut channel thickness when calculating flange thickness.



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

