


Hammer-On Flange Clip, Vertical Mount with Stud



CARACTERISTICI

Can be used to support boxes, fixtures or other applications from beam flanges

Captive threaded stud minimizes the need for additional hardware


Fits most beams

Requires only a hammer to install

Material: Spring Oțel;Oțel
Finish: nVent CADDY Armour;Electrogalvanized

SPECIFICAȚII

Număr de catalog	Article Number	Flange Thickness (FT)	Screw Diameter (Sc)	Screw Length (L)	Static Load
4H24IM11	170140	3 - 8 mm	6	11mm	150N
4H58IM11	170160	8 - 14 mm	6	11mm	150N



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

