

# HD NI Heavy Duty Pipe Clamp, Fire/Sprinkler

## CARACTERISTICI

Fillet welded connector nut has flats to accommodate spanners



**Material:** Oțel



## SPECIFICAȚII

Table 1/4

| Număr de catalog | Article Number | Nut Included | Finish             | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|------------------|----------------|--------------|--------------------|---------------------|-------|---------------|
| HDN024HD         | 575002         | Yes          | Hot-Dip Galvanized | 20 - 24 mm          | 15    | M8, M10       |
| HDN030           | 577003         | Yes          | Electrogalvanized  | 25 - 30 mm          | 20    | M8, M10       |
| HDN035           | 577004         | Yes          | Electrogalvanized  | 31 - 35 mm          | 25    | M8, M10       |
| HDN045HD         | 575006         | Yes          | Hot-Dip Galvanized | 40 - 45 mm          | 32    | M8, M10       |
| HDN059           | 577008         | Yes          | Electrogalvanized  | 54 - 59 mm          |       | M8, M10       |
| HDN059HD         | 575008         | Yes          | Hot-Dip Galvanized | 54 - 59 mm          |       | M8, M10       |
| HDN102           | 577014         | Yes          | Electrogalvanized  | 95 - 102 mm         |       | M10, M12      |
| HDN108           | 577015         | Yes          | Electrogalvanized  | 102 - 108 mm        |       | M10, M12      |
| HDN129HD         | 575018         | Yes          | Hot-Dip Galvanized | 124 - 129 mm        |       | M10, M12      |
| HDN140           | 577019         | Yes          | Electrogalvanized  | 133 - 140 mm        |       | M10, M12      |
| HDN155           | 577021         | Yes          | Electrogalvanized  | 149 - 155 mm        |       | M12, M16      |

| Număr de catalog | Article Number | Nut Included | Finish             | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|------------------|----------------|--------------|--------------------|---------------------|-------|---------------|
| HDN173           | 577023         | Yes          | Electrogalvanized  | 167 - 173 mm        | 150   | M12, M16      |
| HDN173HD         | 575023         | Yes          | Hot-Dip Galvanized | 167 - 173 mm        | 150   | M12, M16      |
| HDN182           | 577024         | Yes          | Electrogalvanized  | 176 - 182 mm        |       | M12, M16      |
| HDN205           | 577026         | Yes          | Electrogalvanized  | 199 - 205 mm        |       | M12, M16      |
| HDN216           | 577027         | Yes          | Electrogalvanized  | 207 - 216 mm        |       | M12, M16      |
| HDN226           | 577028         | Yes          | Electrogalvanized  | 219 - 226 mm        | 200   | M12, M16      |
| HDN226HD         | 575028         | Yes          | Hot-Dip Galvanized | 219 - 226 mm        | 200   | M12, M16      |
| HDN236           | 577029         | Yes          | Electrogalvanized  | 227 - 236 mm        |       | M16, M20      |
| HDN316           | 577068         | Yes          | Electrogalvanized  | 305 - 316 mm        |       | M16, M20      |

Table 2/4

| Număr de catalog | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|------------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN020EG         | 579042         | Yes          | Electrogalvanized | 26 - 31 mm          | 20    | M8, M10       |
| HDN020G          | 579122         | Yes          | GEOMET® 321       | 26 - 31 mm          | 20    | M8, M10       |
| HDN025EG         | 579043         | Yes          | Electrogalvanized | 31 - 37 mm          |       | M8, M10       |
| HDN025G          | 579123         | Yes          | GEOMET® 321       | 31 - 37 mm          |       | M8, M10       |
| HDN032EG         | 579044         | Yes          | Electrogalvanized | 38 - 44 mm          | 32    | M8, M10       |
| HDN032G          | 579124         | Yes          | GEOMET® 321       | 38 - 44 mm          | 32    | M8, M10       |
| HDN040EG         | 579045         | Yes          | Electrogalvanized | 46 - 53 mm          | 40    | M8, M10       |
| HDN040G          | 579125         | Yes          | GEOMET® 321       | 46 - 53 mm          | 40    | M8, M10       |
| HDN047EG         | 579046         | Yes          | Electrogalvanized | 54 - 60 mm          |       | M8, M10       |
| HDN047G          | 579126         | Yes          | GEOMET® 321       | 54 - 60 mm          |       | M8, M10       |
| HDN050EG         | 579047         | Yes          | Electrogalvanized | 60 - 68 mm          | 50    | M8, M10       |
| HDN050G          | 579127         | Yes          | GEOMET® 321       | 60 - 68 mm          | 50    | M8, M10       |
| HDN060EG         | 579048         | Yes          | Electrogalvanized | 66 - 73 mm          |       | M8, M10       |
| HDN060G          | 579128         | Yes          | GEOMET® 321       | 66 - 73 mm          |       | M8, M10       |
| HDN065EG         | 579049         | Yes          | Electrogalvanized | 74 - 81 mm          | 65    | M10, M12      |
| HDN065G          | 579129         | Yes          | GEOMET® 321       | 74 - 81 mm          | 65    | M10, M12      |
| HDN075EG         | 579051         | Yes          | Electrogalvanized | 82 - 88 mm          |       | M10, M12      |
| HDN075G          | 579131         | Yes          | GEOMET® 321       | 82 - 88 mm          |       | M10, M12      |
| HDN080EG         | 579052         | Yes          | Electrogalvanized | 88 - 97 mm          | 80    | M10, M12      |
| HDN080G          | 579132         | Yes          | GEOMET® 321       | 88 - 97 mm          | 80    | M10, M12      |

Table 3/4

| Număr de catalog | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|------------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN085EG         | 579053         | Yes          | Electrogalvanized | 93 - 100 mm         |       | M10, M12      |
| HDN085G          | 579133         | Yes          | GEOMET® 321       | 93 - 100 mm         |       | M10, M12      |
| HDN095EG         | 579054         | Yes          | Electrogalvanized | 101 - 109 mm        |       | M10, M12      |
| HDN095G          | 579134         | Yes          | GEOMET® 321       | 101 - 109 mm        |       | M10, M12      |
| HDN100EG         | 579055         | Yes          | Electrogalvanized | 110 - 118 mm        | 100   | M10, M12      |
| HDN100G          | 579135         | Yes          | GEOMET® 321       | 110 - 118 mm        | 100   | M10, M12      |
| HDN110EG         | 579056         | Yes          | Electrogalvanized | 116 - 126 mm        |       | M10, M12      |
| HDN110G          | 579136         | Yes          | GEOMET® 321       | 116 - 126 mm        |       | M10, M12      |
| HDN120EG         | 579057         | Yes          | Electrogalvanized | 130 - 141 mm        |       | M12, M16      |
| HDN120G          | 579137         | Yes          | GEOMET® 321       | 130 - 141 mm        |       | M12, M16      |
| HDN125EG         | 579058         | Yes          | Electrogalvanized | 136 - 147 mm        | 125   | M12, M16      |
| HDN125G          | 579138         | Yes          | GEOMET® 321       | 136 - 147 mm        | 125   | M12, M16      |
| HDN140EG         | 579059         | Yes          | Electrogalvanized | 144 - 154 mm        |       | M12, M16      |
| HDN140G          | 579139         | Yes          | GEOMET® 321       | 144 - 154 mm        |       | M12, M16      |
| HDN150EG         | 579061         | Yes          | Electrogalvanized | 160 - 169 mm        | 150   | M12, M16      |
| HDN150G          | 579141         | Yes          | GEOMET® 321       | 160 - 169 mm        | 150   | M12, M16      |
| HDN180EG         | 579062         | Yes          | Electrogalvanized | 170 - 180 mm        |       | M12, M16      |
| HDN180G          | 579142         | Yes          | GEOMET® 321       | 170 - 180 mm        |       | M12, M16      |
| HDN190EG         | 579063         | Yes          | Electrogalvanized | 202 - 214 mm        |       | M12, M16      |
| HDN190G          | 579143         | Yes          | GEOMET® 321       | 202 - 214 mm        |       | M12, M16      |

Table 4/4

| Număr de catalog | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|------------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN200EG         | 579064         | Yes          | Electrogalvanized | 219 - 230 mm        | 200   | M12, M16      |
| HDN200G          | 579144         | Yes          | GEOMET® 321       | 219 - 230 mm        | 200   | M12, M16      |
| HDN250EG         | 579065         | Yes          | Electrogalvanized | 273 - 283 mm        | 250   | M20           |
| HDN250G          | 579145         | Yes          | GEOMET® 321       | 273 - 283 mm        | 250   | M20           |
| HDN300EG         | 579066         | Yes          | Electrogalvanized | 317 - 333 mm        | 300   | M20           |
| HDN300G          | 579146         | Yes          | GEOMET® 321       | 317 - 333 mm        | 300   | M20           |
| HDN350EG         | 579067         | Yes          | Electrogalvanized | 349 - 365 mm        | 350   | M20           |
| HDN350G          | 579147         | Yes          | GEOMET® 321       | 349 - 365 mm        | 350   | M20           |
| HDN400EG         | 579068         | Yes          | Electrogalvanized | 395 - 411 mm        | 400   | M20           |
| HDN400G          | 579148         | Yes          | GEOMET® 321       | 395 - 411 mm        | 400   | M20           |
| HDN450EG         | 579069         | Yes          | Electrogalvanized | 447 - 463 mm        | 450   | M20           |
| HDN450G          | 579149         | Yes          | GEOMET® 321       | 447 - 463 mm        | 450   | M20           |

| Număr de catalog | Article Number | Nut Included | Finish            | Outer Diameter (OD) | NB/DN | Rod Size (RS) |
|------------------|----------------|--------------|-------------------|---------------------|-------|---------------|
| HDN500EG         | 579071         | Yes          | Electrogalvanized | 499 - 512 mm        | 500   | M20           |
| HDN500G          | 579151         | Yes          | GEOMET® 321       | 499 - 512 mm        | 500   | M20           |
| HDN015EG         | 579041         | Yes          | Electrogalvanized | 18 - 23 mm          | 15    | M8, M10       |
| HDN015G          | 579121         | Yes          | Electrogalvanized | 18 - 23 mm          | 15    | M8, M10       |

Table 1/4

| Număr de catalog | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|------------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN024HD         | 575002         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN030           | 577003         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN035           | 577004         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN045HD         | 575006         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN059           | 577008         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN059HD         | 575008         | 30 mm     | 2.5 mm        | 6 mm                | M6                         | 30mm             |
| HDN102           | 577014         | 30 mm     | 3 mm          | 8 mm                | M8                         | 40mm             |
| HDN108           | 577015         | 30 mm     | 3 mm          | 8 mm                | M8                         | 40mm             |
| HDN129HD         | 575018         | 30 mm     | 3 mm          | 8 mm                | M8                         | 40mm             |
| HDN140           | 577019         | 40 mm     | 4 mm          | 8 mm                | M8                         | 40mm             |
| HDN155           | 577021         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN173           | 577023         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN173HD         | 575023         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN182           | 577024         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN205           | 577026         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN216           | 577027         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN226           | 577028         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN226HD         | 575028         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN236           | 577029         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN316           | 577068         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |

Table 2/4

| Număr de catalog | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|------------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN020EG         | 579042         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN020G          | 579122         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN025EG         | 579043         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN025G          | 579123         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |

| Număr de catalog | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|------------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN032EG         | 579044         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN032G          | 579124         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN040EG         | 579045         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN040G          | 579125         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN047EG         | 579046         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN047G          | 579126         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN050EG         | 579047         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN050G          | 579127         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN060EG         | 579048         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN060G          | 579128         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN065EG         | 579049         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN065G          | 579129         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN075EG         | 579051         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN075G          | 579131         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN080EG         | 579052         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN080G          | 579132         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |

Table 3/4

| Număr de catalog | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|------------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN085EG         | 579053         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN085G          | 579133         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN095EG         | 579054         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN095G          | 579134         | 30 mm     | 3 mm          | 8 mm                | M8                         | 25mm             |
| HDN100EG         | 579055         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN100G          | 579135         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN110EG         | 579056         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN110G          | 579136         | 30 mm     | 3 mm          | 10 mm               | M10                        | 40mm             |
| HDN120EG         | 579057         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN120G          | 579137         | 40 mm     | 4 mm          | 10 mm               | M10                        | 40mm             |
| HDN125EG         | 579058         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN125G          | 579138         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN140EG         | 579059         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN140G          | 579139         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN150EG         | 579061         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |

| Număr de catalog | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|------------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN150G          | 579141         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN180EG         | 579062         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN180G          | 579142         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN190EG         | 579063         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN190G          | 579143         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |

Table 4/4

| Număr de catalog | Article Number | Width (W) | Thickness (T) | Screw Diameter (Sc) | Screw Diameter metric (Sc) | Screw Length (L) |
|------------------|----------------|-----------|---------------|---------------------|----------------------------|------------------|
| HDN200EG         | 579064         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN200G          | 579144         | 40 mm     | 4 mm          | 12 mm               | M12                        | 40mm             |
| HDN250EG         | 579065         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN250G          | 579145         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN300EG         | 579066         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN300G          | 579146         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN350EG         | 579067         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN350G          | 579147         | 50 mm     | 5 mm          | 16 mm               | M16                        | 60mm             |
| HDN400EG         | 579068         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN400G          | 579148         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN450EG         | 579069         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN450G          | 579149         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN500EG         | 579071         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN500G          | 579151         | 60 mm     | 6 mm          | 16 mm               | M16                        | 60mm             |
| HDN015EG         | 579041         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |
| HDN015G          | 579121         | 25 mm     | 2 mm          | 8 mm                | M8                         | 25mm             |

Table 1/4

| Număr de catalog | Article Number | Static Load | Certifications                                              |
|------------------|----------------|-------------|-------------------------------------------------------------|
| HDN024HD         | 575002         | 2000N       |                                                             |
| HDN030           | 577003         | 2000N       | VdS G4090030, FM Approved, Pipe Hanger Components, ITB      |
| HDN035           | 577004         | 2000N       | FM Approved, Pipe Hanger Components, VdS G4090030, ITB      |
| HDN045HD         | 575006         | 2000N       | VdS G4090030, FM Approved, Pipe Hanger Components           |
| HDN059           | 577008         | 2000N       | VdS G4090030, ITB                                           |
| HDN059HD         | 575008         | 2000N       | VdS G4090030                                                |
| HDN102           | 577014         | 3500N       | AON Fire Protection, BB019, pipe hangers, VdS G4090030, ITB |

| Număr de catalog | Article Number | Static Load | Certifications                                                                                   |
|------------------|----------------|-------------|--------------------------------------------------------------------------------------------------|
| HDN108           | 577015         | 3500N       | VdS G4090030, ITB, AON Fire Protection, BB019, pipe hangers                                      |
| HDN129HD         | 575018         | 5000N       | VdS G4090030                                                                                     |
| HDN140           | 577019         | 5000N       | ITB, AON Fire Protection, BB019, pipe hangers, VdS G4090030                                      |
| HDN155           | 577021         | 5000N       | ITB, AON Fire Protection, BB019, pipe hangers, VdS G4090030                                      |
| HDN173           | 577023         | 5000N       | AON Fire Protection, BB019, pipe hangers, FM Approved, Pipe Hanger Components, VdS G4090030, ITB |
| HDN173HD         | 575023         | 5000N       | FM Approved, Pipe Hanger Components, VdS G4090030                                                |
| HDN182           | 577024         | 8500N       | ITB                                                                                              |
| HDN205           | 577026         | 8500N       | ITB                                                                                              |
| HDN216           | 577027         | 8500N       | ITB                                                                                              |
| HDN226           | 577028         | 8500N       | ITB, VdS G4090030                                                                                |
| HDN226HD         | 575028         | 8500N       | VdS G4090030                                                                                     |
| HDN236           | 577029         | 10000N      | ITB                                                                                              |
| HDN316           | 577068         | 10000N      | ITB                                                                                              |

Table 2/4

| Număr de catalog | Article Number | Static Load | Certifications                      |
|------------------|----------------|-------------|-------------------------------------|
| HDN020EG         | 579042         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN020G          | 579122         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN025EG         | 579043         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN025G          | 579123         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN032EG         | 579044         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN032G          | 579124         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN040EG         | 579045         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN040G          | 579125         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN047EG         | 579046         | 2000N       |                                     |
| HDN047G          | 579126         | 2000N       |                                     |
| HDN050EG         | 579047         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN050G          | 579127         | 2000N       | FM Approved, Pipe Hanger Components |
| HDN060EG         | 579048         | 3500N       |                                     |
| HDN060G          | 579128         | 3500N       |                                     |
| HDN065EG         | 579049         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN065G          | 579129         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN075EG         | 579051         | 3500N       |                                     |
| HDN075G          | 579131         | 3500N       |                                     |

| Număr de catalog | Article Number | Static Load | Certifications                      |
|------------------|----------------|-------------|-------------------------------------|
| HDN080EG         | 579052         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN080G          | 579132         | 3500N       | FM Approved, Pipe Hanger Components |

Table 3/4



| Număr de catalog | Article Number | Static Load | Certifications                      |
|------------------|----------------|-------------|-------------------------------------|
| HDN085EG         | 579053         | 3500N       |                                     |
| HDN085G          | 579133         | 3500N       |                                     |
| HDN095EG         | 579054         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN095G          | 579134         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN100EG         | 579055         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN100G          | 579135         | 3500N       | FM Approved, Pipe Hanger Components |
| HDN110EG         | 579056         | 5000N       |                                     |
| HDN110G          | 579136         | 5000N       |                                     |
| HDN120EG         | 579057         | 5000N       |                                     |
| HDN120G          | 579137         | 5000N       |                                     |
| HDN125EG         | 579058         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN125G          | 579138         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN140EG         | 579059         | 5000N       |                                     |
| HDN140G          | 579139         | 5000N       |                                     |
| HDN150EG         | 579061         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN150G          | 579141         | 5000N       | FM Approved, Pipe Hanger Components |
| HDN180EG         | 579062         | 8500N       |                                     |
| HDN180G          | 579142         | 8500N       |                                     |
| HDN190EG         | 579063         | 8500N       |                                     |
| HDN190G          | 579143         | 8500N       |                                     |

Table 4/4

| Număr de catalog | Article Number | Static Load | Certifications |
|------------------|----------------|-------------|----------------|
| HDN200EG         | 579064         | 8500N       |                |
| HDN200G          | 579144         | 8500N       |                |
| HDN250EG         | 579065         | 10000N      |                |
| HDN250G          | 579145         | 10000N      |                |
| HDN300EG         | 579066         | 12500N      |                |
| HDN300G          | 579146         | 12500N      |                |
| HDN350EG         | 579067         | 12500N      |                |
| HDN350G          | 579147         | 12500N      |                |

| Număr de catalog | Article Number | Static Load | Certifications |
|------------------|----------------|-------------|----------------|
| HDN400EG         | 579068         | 12500N      |                |
| HDN400G          | 579148         | 12500N      |                |
| HDN450EG         | 579069         | 12500N      |                |
| HDN450G          | 579149         | 12500N      |                |
| HDN500EG         | 579071         | 12500N      |                |
| HDN500G          | 579151         | 12500N      |                |
| HDN015EG         | 579041         | 2000N       |                |
| HDN015G          | 579121         | 2000N       |                |

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

