

Heavy Duty Pipe Clamp

CARACTERISTICI

For high static requirements in industrial construction

Suitable for fix point applications



Material: Oțel
Finish: Painted;Red Oxide

SPECIFICAȚII

Table 1/2

Număr de catalog	Article Number	Outer Diameter (OD)	NB/D N	Hole Size (HS)	Screw Diameter (Sc)	Screw Length (L)
SSG022RO	574600	20.5 - 22 mm	15	6.6 mm	6 mm	20mm
SSG028RO	574610	26.5 - 28 mm	20	6.6 mm	6 mm	20mm
SSG0359RO	574725	355 - 363 mm		22 mm	20 mm	80mm
SSG035RO	574620	33 - 35 mm	25	11 mm	10 mm	40mm
SSG043RO	574630	40 - 43 mm	32	11 mm	10 mm	40mm
SSG049RO	574640	48 - 49 mm	40	11 mm	10 mm	40mm
SSG061RO	574650	57.0 - 60.3 mm	50	11 mm	10 mm	40mm
SSG077RO	574660	75 - 77 mm	65	11 mm	10 mm	40mm
SSG090RO	574670	88 - 90 mm	80	11 mm	10 mm	40mm
SSG115RO	574680	110 - 115 mm	100	18 mm	16 mm	60mm
SSG141RO	574685	139 - 141 mm	125	18 mm	16 mm	60mm
SSG170RO	574690	165 - 170 mm	150	18 mm	16 mm	60mm




Număr de catalog	ArticleNumber	Outer Diameter(OD)	NB/D N	Hole Size(HS)	Screw Diameter(Sc)	Screw Length(L)
SSG222R0	574700	216 - 222 mm	200	22 mm	20 mm	80mm
SSG276R0	574710	267 - 276 mm	250	22 mm	20 mm	80mm
SSG327R0	574720	321 - 327 mm	300	22 mm	20 mm	80mm
SSG410R0	574730	403 - 410 mm	400	26 mm	24 mm	80mm

Table 2/2					
Număr de catalog	Article Number	Static Load	Width (W)	Thickness (T)	A
SSG022R0	574600	1000N	23 mm	3 mm	46 mm
SSG028R0	574610	1000N	23 mm	3 mm	52 mm
SSG0359R0	574725	2600N	60 mm	8 mm	427 mm
SSG035R0	574620	1000N	40 mm	4 mm	71 mm
SSG043R0	574630	1000N	40 mm	4 mm	79 mm
SSG049R0	574640	1000N	40 mm	4 mm	85 mm
SSG061R0	574650	1800N	40 mm	4 mm	97 mm
SSG077R0	574660	1400N	40 mm	4 mm	113 mm
SSG090R0	574670	1200N	40 mm	4 mm	126 mm
SSG115R0	574680	2900N	50 mm	6 mm	167 mm
SSG141R0	574685	2500N	50 mm	6 mm	193 mm
SSG170R0	574690	2200N	50 mm	6 mm	222 mm
SSG222R0	574700	3600N	60 mm	8 mm	290 mm
SSG276R0	574710	3100N	60 mm	8 mm	344 mm
SSG327R0	574720	2800N	60 mm	8 mm	395 mm
SSG410R0	574730	4100N	70 mm	10 mm	492 mm

DETALII SUPLIMENTARE DESPRE PRODUS

Static load refers to a complete set of Heavy Duty Pipe Clamps held in place with indicated screws per ISO 4014 and corresponding hex nuts per ISO 4032 (for further information, please refer to Standard SSG 7075E).

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDDT

