

Internal Strut Beam Clamp with Bolt



CARACTERISTICI

U-shaped clip for clamping the back of strut channel to a beam

Hex bolt included

Requires installation in pairs


SPECIFICAȚII

Număr de catalog	Article Number	Material	Finish	Flange Thickness (FT)	Width (W)	Screw Diameter (Sc)	Static Load
ZT606HDEG	313270	Oțel	Hot-Dip Galvanized, Electrogalvanized	28 mm Max	30 mm	10	2900N

DETALII SUPLIMENTARE DESPRE PRODUS

Static Load is based on one pair of Strut Beam Clamps.

Include strut channel thickness when calculating flange thickness.



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

