

# nVent CADDY Speed Link SLK with Threaded Stud End



## CARACTERISTICI

Complete system includes wire, locking device and pre-assembled threaded stud end fitting

Attaches to structures with threaded anchors or devices with threaded hole

Connects directly to threaded devices in trapeze assemblies, light fixtures, HVAC assemblies or signage

**Material:** Oțel; Polypropylene; Zinc Alloy  
**Finish:** Electrogalvanized  
**Static Load Safety Factor:** 5:1  
**Complies With:** SMACNA HVAC-DCS



## SPECIFICAȚII

Table 1/2


| Număr de catalog | Article Number | Wire Rope Diameter | Wire Rope Length | Rod Size (RS) | Screw Length (L) | Height (H) |
|------------------|----------------|--------------------|------------------|---------------|------------------|------------|
| SLK15L1SEM6      | 196564         | 1.5 mm             | 1m               | 6             | 25mm             | 55 mm      |
| SLK15L1SEM8      | 196565         | 1.5 mm             | 1m               | 8             | 45mm             | 55 mm      |
| SLK15L2SEM6      | 196566         | 1.5 mm             | 2m               | 6             | 25mm             | 55 mm      |
| SLK15L2SEM8      | 196567         | 1.5 mm             | 2m               | 8             | 45mm             | 55 mm      |
| SLK15L3SEM6      | 196568         | 1.5 mm             | 3m               | 6             | 25mm             | 55 mm      |
| SLK15L3SEM8      | 196570         | 1.5 mm             | 3m               | 8             | 45mm             | 55 mm      |
| SLK2L2SEM8       | 196559         | 2 mm               | 2m               | 8             | 45mm             | 55 mm      |
| SLK2L3SEM8       | 196561         | 2 mm               | 3m               | 8             | 45mm             | 55 mm      |
| SLK2L5SEM6       | 196562         | 2 mm               | 5m               | 6             | 25mm             | 55 mm      |

| Număr de catalog | ArticleNumber | Wire RopeDiameter | Wire RopeLength | Rod Size(RS) | Screw Length(L) | Height(H) |
|------------------|---------------|-------------------|-----------------|--------------|-----------------|-----------|
| SLK2L5SEM8       | 196563        | 2 mm              | 5m              | 8            | 45mm            | 55 mm     |

Table 2/2

| Număr de catalog | Article Number | Width (W) | Thickness (T) | Angle (a) | Static Load |
|------------------|----------------|-----------|---------------|-----------|-------------|
| SLK15L1SEM6      | 196564         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L1SEM8      | 196565         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L2SEM6      | 196566         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L2SEM8      | 196567         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L3SEM6      | 196568         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK15L3SEM8      | 196570         | 19 mm     | 12.5 mm       | 90 ° Max  | 195N        |
| SLK2L2SEM8       | 196559         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |
| SLK2L3SEM8       | 196561         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |
| SLK2L5SEM6       | 196562         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |
| SLK2L5SEM8       | 196563         | 19 mm     | 12.5 mm       | 90 ° Max  | 440N        |

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

