

# nVent CADDY Speed Link SLS with Hook



## CARACTERISTICI

Complete system includes wire, locking device and pre-assembled hook end fitting

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide secure connection

Insert cable through hole and use bottom side of hook as an end stop

Finger tightening of nut secures the locking device into position without tools

Installs in strut profiles without the need to insert fingers or tools into the strut

**Material:** Oțel; Zinc Alloy; Polypropylene  
**Finish:** Electrogalvanized  
**Static Load Safety Factor:** 5:1  
**Complies With:** SMACNA HVAC-DCS



## SPECIFICAȚII

Table 1/3

| Număr de catalog | Article Number | Wire Rope Diameter | Wire Rope Length | A       | B       | C      |
|------------------|----------------|--------------------|------------------|---------|---------|--------|
| SLS2L1           | 196741         | 2 mm               | 1m               | 57 mm   | 20 mm   | 5.5 mm |
| SLS2L10          | 196746         | 2 mm               | 10m              | 57 mm   | 20 mm   | 5.5 mm |
| SLS2L2           | 196742         | 2 mm               | 2m               | 57 mm   | 20 mm   | 5.5 mm |
| SLS3L10          | 196752         | 3 mm               | 10m              | 57.6 mm | 23.2 mm | 6.1 mm |
| SLS3L3           | 196749         | 3 mm               | 3m               | 57.6 mm | 23.2 mm | 6.1 mm |
| SLS3L5           | 196750         | 3 mm               | 5m               | 57.6 mm | 23.2 mm | 6.1 mm |

Table 2/3

| Număr de catalog | Article Number | Height 1 (H1) | Height 2 (H2) | Thread Size (TS) | Width (W) | Hole Size (HS) |
|------------------|----------------|---------------|---------------|------------------|-----------|----------------|
| SLS2L1           | 196741         | 53mm          | 43.5mm        | M8               | 16 mm     | 8 - 10 mm      |
| SLS2L10          | 196746         | 53mm          | 43.5mm        | M8               | 16 mm     | 8 - 10 mm      |

| Număr de catalog | Article Number | Height 1 (H1) | Height 2 (H2) | Thread Size (TS) | Width (W) | Hole Size (HS) |
|------------------|----------------|---------------|---------------|------------------|-----------|----------------|
| SLS2L2           | 196742         | 53mm          | 43.5mm        | M8               | 16 mm     | 8 - 10 mm      |
| SLS3L10          | 196752         | 53mm          | 46.5mm        | M12              | 20 mm     | 12 - 14 mm     |
| SLS3L3           | 196749         | 53mm          | 46.5mm        | M12              | 20 mm     | 12 - 14 mm     |
| SLS3L5           | 196750         | 53mm          | 46.5mm        | M12              | 20 mm     | 12 - 14 mm     |

| Table 3/3        |                |                         |               |             |
|------------------|----------------|-------------------------|---------------|-------------|
| Număr de catalog | Article Number | Slot Size (SS)          | Thickness (T) | Static Load |
| SLS2L1           | 196741         | 8 x 6.5 mm - 8 x 10 mm  | 4 mm Max      | 270N        |
| SLS2L10          | 196746         | 8 x 6.5 mm - 8 x 10 mm  | 4 mm Max      | 270N        |
| SLS2L2           | 196742         | 8 x 6.5 mm - 8 x 10 mm  | 4 mm Max      | 270N        |
| SLS3L10          | 196752         | 12 x 10 mm - 12 x 14 mm | 6 mm Max      | 670N        |
| SLS3L3           | 196749         | 12 x 10 mm - 12 x 14 mm | 6 mm Max      | 670N        |
| SLS3L5           | 196750         | 12 x 10 mm - 12 x 14 mm | 6 mm Max      | 670N        |



## DETALII SUPLIMENTARE DESPRE PRODUS


The 2 mm locking device is compatible with C-Channel Types E0 and E0L.

The 3 mm locking device is compatible with C-Channel Types E1, E2, E2L, E3, E4, E5, Strut Channel Type C, Slotted, Strut Channel Type A, Slotted, Strut Channel Type AS, Perforated, Strut Channel Type CC, Slotted, Strut Channel Type AA, Slotted.

Total load per wire on a multi-tier trapeze must not exceed static load.

## DIAGRAMS





## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

