

# nVent CADDY Superfix 243 M8



## CARACTERISTICI

Includes easy closing mechanism

Combo head bolt works with slotted, hex, or Phillips drivers

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1

**Material:** Oțel;EPDM-SBR Rubber  
**Finish:** Electrogalvanized  
**Color:** Black  
**Temperature:** -50 to 110 °C



## SPECIFICAȚII

Table 1/2

| Număr de catalog | Article Number | Outer Diameter (OD) | NB/DN | Rod Size (RS) | Width (W) | Thickness (T) |
|------------------|----------------|---------------------|-------|---------------|-----------|---------------|
| SXE019           | 400056         | 15 - 19 mm          | 10    | M8            | 20 mm     | 1.5 mm        |
| SXE023           | 400057         | 21 - 23 mm          | 15    | M8            | 20 mm     | 1.5 mm        |
| SXE028           | 400058         | 26 - 28 mm          | 20    | M8            | 20 mm     | 1.5 mm        |
| SXE035           | 400059         | 32 - 35 mm          | 25    | M8            | 20 mm     | 1.5 mm        |
| SXE043           | 400060         | 40 - 43 mm          | 32    | M8            | 20 mm     | 1.5 mm        |
| SXE052           | 400062         | 48 - 52 mm          | 40    | M8            | 20 mm     | 1.5 mm        |
| SXE058           | 589310         | 54 - 58 mm          |       | M8            | 20 mm     | 2 mm          |
| SXE061           | 589320         | 57 - 61 mm          | 50    | M8            | 20 mm     | 2 mm          |
| SXE014           | 400055         | 12 - 14 mm          | 8     | M8            | 20 mm     | 1.5 mm        |


Table 2/2

| Număr de catalog | Article Number | Screw Diameter (Sc) | Screw Length (L) | Static Load |
|------------------|----------------|---------------------|------------------|-------------|
| SXE019           | 400056         | 6                   | 27mm             | 1000N       |
| SXE023           | 400057         | 6                   | 27mm             | 1000N       |
| SXE028           | 400058         | 6                   | 27mm             | 1000N       |
| SXE035           | 400059         | 6                   | 27mm             | 1000N       |
| SXE043           | 400060         | 6                   | 32mm             | 1000N       |
| SXE052           | 400062         | 6                   | 32mm             | 1300N       |
| SXE058           | 589310         | 6                   | 32mm             | 1300N       |
| SXE061           | 589320         | 6                   | 32mm             | 1300N       |
| SXE014           | 400055         | 6                   | 27mm             | 1000N       |

## DETALII SUPLIMENTARE DESPRE PRODUS

Lining is EPDM rubber.

## DIAGRAMS



## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răni corporale grave și moarte și/sau poate anula garanția dvs.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

