


PEMSA Wire Basket Tray Quick Coupler



CARACTERISTICI

Easy to use, quick connect feature

No additional hardware

Works with wide range of tray sizes and configurations


IEC 61537 load rating and earthing compliant

Material: Oțel
Finish: Electrogalvanized



SPECIFICAȚII

Număr de catalog	Article Number	Color	Length (L)	Width 1 (W1)	Width 2 (W2)	Height (H)	Diameter (Ø)
WBTQSPL45BG	820721	Black	97mm	23.5 mm	33.5 mm	13 mm	4.0 - 4.5 mm
WBTQSPL45EG	820720		97mm	23.5 mm	33.5 mm	13 mm	4.0 - 4.5 mm
WBTQSPL5BG	820723	Black	97mm	23.5 mm	33.5 mm	13 mm	5 mm
WBTQSPL5EG	820722		97mm	23.5 mm	33.5 mm	13 mm	5 mm



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

