

Saddle Washer

CARACTERISTICI



U-shaped wrap around washer



SPECIFICAȚII

Număr de catalog	Article Number	Material	Finish	Hole Size (HS)	Thickness (T)	A	B
PLN10	589930	Oțel	Electro galvaniz ed	10.5 mm	3 mm	42 mm	30 mm
PLN11S6	589928	Stainless Steel 316 (EN 1.4401)		11 mm	3 mm	42 mm	50 mm
PLN13	589940	Oțel	Electro galvaniz ed	13 mm	3 mm	42 mm	30 mm
PLN13HD	589949	Oțel	Hot-Dip Galvanized	13 mm	3 mm	42 mm	30 mm
PLN8	589925	Oțel	Electro galvaniz ed	8.4 mm	3 mm	42 mm	30 mm

DIAGRAMS



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/GRDDT

