

Speedway Cable Ladder Outside Riser, 90°



CARACTERISTICI

Creates a 90° outside riser elevation change for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant



Responsive design and layout services, including seismic

Material: Oțel
Finish: Hot-Dip Galvanized



SPECIFICAȚII

Număr de catalog	Article Number	Width (W)	Angle (a)	A	B	C	D
CL110X150OR90HD	840600	150 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X300OR90HD	840610	300 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X450OR90HD	840620	450 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X600OR90HD	840630	600 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X750OR90HD	840640	750 mm	90 °	410 mm	410 mm	580 mm	80 mm
CL110X900OR90HD	840650	900 mm	90 °	410 mm	410 mm	580 mm	80 mm



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

