

Strut to Strut Connector



CARACTERISTICI

Consists of two halve castings, nut and bolt

Allows for bolting two strut channels back to back through the slots

SPECIFICAȚII

Table 1/2

Număr de catalog	Article Number	Material	Finish	A	B	C
STS	315450	Oțel	Electrogalvanized	32 mm	25 mm	12.7 mm


Table 2/2

Număr de catalog	Article Number	Torque (TQ)	Static Load
STS	315450	7 N·m	4900N

DETALII SUPLIMENTARE DESPRE PRODUS

Minimum of 2 required. Maximum spacing 1 foot (300mm).

Minimum half-slot dimensions 9/16" x 7/8" (14.3 mm x 22.2 mm).



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

