

TBHKM Trapezoidal Deck Hanger with Fixed Nut



CARACTERISTICI

Requires separate cross bolt and nut

Use TDHP perforation tool to punch hole in decking

Material: Oțel
Finish: Electrogalvanized





SPECIFICAȚII

Table 1/2

Număr de catalog	Article Number	Rod Size (RS)	A	B	C	Thickness (T)
TBHKM10	597583	10	97 mm	91.5 mm	25 mm	2.5 mm
TBHKM8	597582	8	97 mm	91.5 mm	25 mm	2.5 mm

Table 2/2

Număr de catalog	Article Number	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Certifications
TBHKM10	597583	10.5 mm	5 mm	FM Approved, Pipe Hanger Components, VdS G4060082, ITB
TBHKM8	597582	10.5 mm	5 mm	VdS G4060082, ITB



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

