


# Vertical Adjustable Coupler



## CARACTERISTICI

Provides high-strength joint with SPEEDWAY Cable Ladder profile

Integral hinge allows simple vertical cable ladder joint adjustments


Installs quickly and easily with included hardware

Multiple slots allow for field adjustments



## SPECIFICAȚII

| Număr de catalog | Article Number | Material | Finish             | Angle (a) | A      | B     | C    |
|------------------|----------------|----------|--------------------|-----------|--------|-------|------|
| CLSW4VACGA       | 842030         | Oțel     | Hot-Dip Galvanized | 0 - 90 °  | 150 mm | 62 mm | 2 mm |



AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

