


19" Front Panel for Thermostat With Digital Display, 1 U



19" Front Panel for Thermostat With Digital Display, 1 U

CARACTERISTICI

19" Front Panel, 1 U, with cut-out for thermostat with digital display

Accessory Type: Front panel



SPECIFICAȚII

Table 1/3

Număr de catalog	Type	Mounting	EMC Shielding	Material	Front Finish	Rear Finish
30118-267	19" Front Panel	Screw-on Front	No	Aluminiu	Anodized	Anodized
30118-315	19" Front Panel	Screw-on Front	No	Aluminiu	Painted	Painted
30118-360	19" Front Panel	Screw-on Front	No	Aluminiu	Painted	Painted

Table 2/3

Număr de catalog	Color Code	Rack Height	Height	Rack Width	Width	Depth
30118-267		1U	35mm		76mm	3mm
30118-315	RAL 7035	1U	43mm	95HP	483mm	3mm
30118-360	RAL 7021	1U	43mm	95HP	483mm	3mm

Table 3/3

Număr de catalog	Package Quantity	Finish
30118-267	1	Anodized
30118-315	1	Vopsit Pulbere

Număr de catalog	Package Quantity	Finish
30118-360	1	Vopsit Pulbere

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.