


# EuropacPRO Perforated Rail for Connector



Perforated flat rail for connector mounting i.a.w. EN 60603-2 and DIN 41612, on VT horizontal rails.

## CARACTERISTICI

In conjunction with rear horizontal rails, VT

For Connector Mounting in accordance with EN 60603-2, DIN 41612

**Finish:** Passivated  
**Material:** Aluminiiu  
**Product Type:** Perforated Rail



## SPECIFICAȚII

| Număr de catalog | Rack Width | Package Quantity | Length       | Product Family                                                    | Works With          | Certifications |
|------------------|------------|------------------|--------------|-------------------------------------------------------------------|---------------------|----------------|
| 20822-046        | 40HP       | 4                | 203.2m<br>m  | EuropacPRO                                                        | Sub racks           | RoHS           |
| 20822-047        | 60HP       | 4                | 304.8m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-048        | 84HP       | 4                | 431.8m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-049        | 28HP       | 4                | 142.24<br>mm | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-050        | 42HP       | 4                | 213.36<br>mm | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases | RoHS           |
| 20822-051        | 20HP       | 4                | 101.6m<br>m  | EuropacPRO                                                        | Sub racks           | RoHS           |
| 20822-052        | 4HP        | 4                | 20.32m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases |                |
| 20822-053        | 8HP        | 4                | 40.64m<br>m  | EuropacPRO, RatiopacPRO, RatiopacPRO<br>AIR, CompacPRO, PropacPRO | Sub racks,<br>Cases |                |

## DETALII SUPLIMENTARE DESPRE PRODUS

---

A threaded insert is required to secure the perforated rail on the horizontal rail.

## AVERTIZARE

---

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.