


Guide Rail Multi Piece, Mid-Piece Aluminium/Plastic Extrusion



Guide rail mid-piece for individual multi-piece guide rails out of plastic or Aluminum extrusion. Suitable for Standard, Accessory, 4.4" PCB types and end pieces with coding.

CARACTERISTICI

Middle profile for mounting guide rails for 2 mm groove width

2 plastic end pieces are required; these are pushed on to both ends of the middle profile

Guide rails can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Storage temperature: from -40 °C ... 130 °C

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Product Type: Guide Rail
Type: Middle Section



SPECIFICAȚII

Table 1/2

Număr de catalog	Board Depth	Groove Width	Color	Material	Package Quantity	Works With
34560-891	160mm	2	Silver	Aluminiu	1	Subracks, Cases, Chassis
34560-892	220mm	2	Silver	Aluminiu	1	Subracks, Cases, Chassis
34560-893	280mm	2	Silver	Aluminiu	1	Subracks, Cases, Chassis
34560-900	1000mm	2	Silver	Aluminiu	1	Subracks, Cases, Chassis
34564-891	160mm	2	Grey	PVC	1	Subracks, Cases, Chassis
34564-892	220mm	2	Grey	PVC	1	Subracks, Cases, Chassis
34564-893	280mm	2	Grey	PVC	1	Subracks, Cases, Chassis
34564-900	1000mm	2	Grey	PVC	1	Subracks, Cases, Chassis

Table 2/2

Număr de catalog	Finish	Color Code
34560-891	Anodized	

Număr de catalog	Finish	Color Code
34560-892	Anodized	
34560-893	Anodized	
34560-900	Anodized	
34564-891		RAL 7035
34564-892		RAL 7035
34564-893		RAL 7035
34564-900		RAL 7035

DETALII SUPLIMENTARE DESPRE PRODUS

Delivery may be in Standard Pack Quantity (SPQ). Pricing is per individual item.

One guide rail consists of 1 pair of head pieces and 1 profile piece.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe www.nvent.com și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

