

# PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

## CARACTERISTICI

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

**EMC Shielding:** Yes  
**Product Type:** Front Panel  
**Type:** Front Panel without Handle



## SPECIFICAȚII

Table 1/2

| Număr de catalog | Package Quantity | Accessory Type | Mounting       | Gasket Type | Front Finish  | Rear Finish   |
|------------------|------------------|----------------|----------------|-------------|---------------|---------------|
| 20835-598        | 1                | Front panel    | Screw-on Front | O-Ring EMC  | Anodized      | Conductive    |
| 20835-889        | 1                | Front panel    | Screw-on Front | O-Ring EMC  | Anodized      | Conductive    |
| 20835-890        | 1                |                | Screw-on Front |             |               |               |
| 20835-893        | 10               |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-922        | 1                |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-923        | 1                |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-924        | 10               |                | Screw-on Front |             | Chrome Plated | Chrome Plated |
| 20835-928        | 10               |                | Screw-on Front |             | Anodized      | Conductive    |

Table 2/2

| Număr de catalog | Treated Edges | Complies With             | Depth | Finish   | Height | Material | Width  |
|------------------|---------------|---------------------------|-------|----------|--------|----------|--------|
| 20835-598        | No            | PMC Mezzanine, IEEE P1386 | 2.5mm | Anodized | 74mm   | Aluminiu | 12.7mm |

| Număr de catalog | Treated Edges | Complies With             | Depth | Finish   | Height | Material | Width  |
|------------------|---------------|---------------------------|-------|----------|--------|----------|--------|
| 20835-889        | No            | PMC Mezzanine, IEEE P1386 | 2.5mm | Anodized | 74mm   | Aluminiu | 12.7mm |
| 20835-890        | No            | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-893        | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-922        | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-923        | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-924        | Yes           | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |
| 20835-928        | No            | PMC Mezzanine, IEEE P1386 |       |          | 74mm   | Zinc     | 12.7mm |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.