


# Rear Panel for RatiopacPRO/PropacPRO, Perforated, Retrofit Shielding



The perforated rear panel, Al, 2.5 mm is unshielded. The rear side is conductive.

## CARACTERISTICI

Rear panel, Al, 2.5 mm, front: anodized, rear: conductive; unshielded

Enables mounting on horizontal rails

|                        |                              |
|------------------------|------------------------------|
| <b>Finish:</b>         | Anodized; Passivated         |
| <b>Material:</b>       | Aluminiu                     |
| <b>Product Family:</b> | RatiopacPRO; RatiopacPRO AIR |
| <b>Product Type:</b>   | Side Panel                   |
| <b>Type:</b>           | Rear Panel                   |
| <b>Works With:</b>     | Cases                        |



## SPECIFICAȚII

| Număr de catalog | Rack Height | Rack Width | Package Quantity | Height  | Width   |
|------------------|-------------|------------|------------------|---------|---------|
| 20848-680        | 2U          | 42HP       | 1                | 83.5mm  | 213mm   |
| 20848-681        | 2U          | 63HP       | 1                | 83.5mm  | 319.7mm |
| 20848-633        | 3U          | 28HP       | 1                | 123.4mm | 141.9mm |
| 20848-634        | 3U          | 42HP       | 1                | 123.4mm | 213mm   |
| 20848-635        | 3U          | 63HP       | 1                | 123.4mm | 319.7mm |
| 20848-636        | 3U          | 84HP       | 1                | 123.4mm | 426.4mm |
| 20848-657        | 4U          | 42HP       | 1                | 168.9mm | 213mm   |
| 20848-658        | 4U          | 63HP       | 1                | 168.9mm | 319.7mm |
| 20848-659        | 4U          | 84HP       | 1                | 168.9mm | 426.4mm |
| 20848-643        | 6U          | 84HP       | 1                | 256mm   | 426.4mm |
| 20848-640        | 6U          | 28HP       | 1                | 256mm   | 141.9mm |

| Număr de catalog | Rack Height | Rack Width | Package Quantity | Height  | Width   |
|------------------|-------------|------------|------------------|---------|---------|
| 20848-641        | 6U          | 42HP       | 1                | 256mm   | 213mm   |
| 20848-642        | 6U          | 63HP       | 1                | 256mm   | 319.7mm |
| 20848-656        | 4U          | 28HP       | 1                | 168.9mm | 141.9mm |
| 20848-679        | 2U          | 28HP       | 1                | 83.5mm  | 141.9mm |
| 20848-682        | 2U          | 84HP       | 1                | 83.5mm  | 426.4mm |
| 20848-744        | 5U          | 28HP       | 1                | 220mm   | 141.9mm |
| 20848-745        | 5U          | 42HP       | 1                | 220mm   | 213mm   |
| 20848-746        | 5U          | 63HP       | 1                | 220mm   | 319.7mm |
| 20848-747        | 5U          | 84HP       | 1                | 220mm   | 426.4mm |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

