

# Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.  
Prepared for high cable densities and 19" integration.

## CARACTERISTICI

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

**Frame Material:** Oțel  
**Material:** Oțel  
**Product Type:** Rack

## SPECIFICAȚII

Table 1/2

| Număr de catalog | Rack Height | Cladding Material | Frame Color | Height | Frame Color Code | Cladding Color |
|------------------|-------------|-------------------|-------------|--------|------------------|----------------|
| 10630-027        | 42U         | Oțel              | Black Grey  | 2000mm | RAL 7021         | Black Grey     |
| 10630-028        | 42U         | Oțel              | Black Grey  | 2000mm | RAL 7021         | Black Grey     |

Table 2/2

| Număr de catalog | Width | Depth  | Static Load | Cladding Color Code | Package Quantity | Dynamic Load | Finish         |
|------------------|-------|--------|-------------|---------------------|------------------|--------------|----------------|
| 10630-027        | 800mm | 1200mm | 1600kg      | RAL 7021            | 1                | 1000kgf      | Vopsit Pulbere |
| 10630-028        | 800mm | 1200mm | 1600kg      | RAL 7021            | 1                | 1000kgf      | Vopsit Pulbere |

## AVERTIZARE

Produsele nVent trebuie instalate și utilizate numai așa cum este indicat în fișele de instrucțiuni și materialele de formare ale nVent. Fișele de instrucțiuni sunt disponibile pe [www.nvent.com](http://www.nvent.com) și de la reprezentantul dvs. de servicii clienți nVent. O instalare incorectă, o utilizare abuzivă, o aplicare greșită sau orice altă lipsă de respectare completă a instrucțiunilor și avertismentelor nVent poate duce la defectarea produsului, la deteriorarea proprietății, la răniri corporale grave și moarte și/sau poate anula garanția dvs.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

