

# T-anslutning

## DESIGN

För 90° ledningsanslutningar



## SPECIFIKATIONER

Table 1/2

| Katalognummer | Artikelnummer | Material | Ledarstorlek           | Djup (D) | Höjd (H) | Bredd (W) |
|---------------|---------------|----------|------------------------|----------|----------|-----------|
| CTR8CU        | 710030        | Mässing  | 8 mm fast, 10 mm, fast | 21mm     | 46 mm    | 40 mm     |

Table 2/2

| Katalognummer | Artikelnummer | nVent ERICO Cu-Bond-ledare | Enhetsvikt | Uppfyller    |
|---------------|---------------|----------------------------|------------|--------------|
| CTR8CU        | 710030        | CBSC10                     | 0.17 kg    | IEC® 62561-1 |

## YTTERLIGARE PRODUKTINFORMATION

IEC-överensstämmelse gäller endast för angivna nVent ERICO Cu-Bond ledningar.



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på [www.nvent.com](http://www.nvent.com) och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

