


Flänsskruv, tvärgående/spårad



Integrated load spreading, replaces separate washer.
Improved joint consistency (less variation from washer misalignment) Better vibration resistance, especially with serrated collars

DESIGN

For assembly of partial width front panels and plug-in units

For EuropacPRO and RatiopacPRO

Cross Recess / Slotted combines advantages of both imprints: it offers a high level of torque to achieve quick and easy installation and enhances rotational leverage. It is convenient to use while offering universal tool compatibility.

Produkttyp: Skruv

Typ: Skruv



SPECIFIKATIONER

Table 1/3

Katalognummer	Diameter	Längd	Material	Yta	Antal i förpackningen	Trådstorlek
21101-101		12.3mm	Stål	Förtennad	100	M2.5
21101-906		12.3mm	Rostfritt stål		100	M2.5
21101-102		12.3mm	Stål	Zinc Plated, Black	100	M2.5
21101-323		11mm			100	M2.5
21102-026	2.5mm	12.3mm	Stål	Förtennad	100	M2.5

Table 2/3

Katalognummer	Djup	Höjd	Bredd	Fungerar med	Trådlängd	Gängtyp
21101-101	14.3mm	5mm	5mm	Frontpaneler	12.3mm	Metrisk
21101-906				Frontpaneler	12.3mm	
21101-102	14.3mm	5mm	5mm	Frontpaneler	12.3mm	Metrisk
21101-323				Frontpaneler		
21102-026				Plugin-enhet av ramtyp, Kassetter	3mm	

Table 3/3

Katalognummer	Vridmoment	Certifieringar
21101-101	0.3N·m	RoHS
21101-906	0.3N·m	RoHS
21101-102	0.3N·m	RoHS
21101-323	0.3N·m	
21102-026	0.3N·m	

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

