

PXI Express-styrenhet, 4 HP, I5-1145G7E 32-1024



KATALOGNUMMER

21265-124

nVent SCHROFFS inbyggda styrenhet är den mest kompakta och kraftfulla 3U-styrenheten med en kortplats för PXI Express- och CPClexp-plattformarna. Med sina enorma och framtidssäkra gränssnittsfunktioner fungerar den perfekt med de flesta test- och mätapplikationer. Styrenheten drivs av 11:e generationens Intel® Core i3/i5-processorer i kombination med upp till 64 GB DDR4-minne och stöder enkelt tillämpningar med hög bandbredd med framtidssäkra PCIe Gen4 och dubbla 2500BASE-T-systemanslutningar.

DESIGN

PXI Express System Controller, 3 U, 4 HP, med Intel Core I5-1145G7E-processor

PXI?-5 PXI Express maskinvaruspecifikation. Kompatibel med Rev.2.0

Maximal PCIe-bandbredd på 14 Gbit/s.

Uppgraderingsbar M.2 NVMe och DDR4-lagring

3x USB3.1, 2x GbE och 1x DP 1,2 på frontpanelen

Fullständigt anpassningsbart AMI Aptio® Embedded BIOS

PRODUKTATTRIBUT

Produkttyp: System

Typ: Reglerenhet

Dataöverföring: PCIe Gen3

Rackhöjd: 3U

Uppfyller: PXISA PXI-5 R1.1

Djup: 160mm

Nettovikt: 0.4kg

Antal i förpackningen: 1

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched

from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Överensstämmer med PICMG rev. 3,0 och PXI-6.

Modifierade styrenheter finns tillgängliga på begäran.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

