


RatiopacPRO, komplett väska, Skrivbordsdator, Skärmad, Frontklädsel, 3 U, 42 HP, 315 mm



KATALOGNUMMER

24572-052

nVent SCHROFF RatiopacPRO-väska med EMC-skärmning skyddar elektroniken för 19-tums och enskilda elektroniska enheter. Det här flexibla och robusta fodralet är enkelt att konvertera från en stationär dator till en 19-tums rackmonterad väska och har fyra olika stilalternativ. Denna version av fodralet ger en elegant design för skrivbordsprogram.

DESIGN

Bordsskåp med förkonfigurerade komponenter, i enlighet med IEC 60297-3-101; förberedd för 19-tums komponenter, t.ex. insticksenheter och eurokort

Skärmad

Version med täcklister

Ventilationsskåra i bottenplattan

Perforerad bakplåt

Överensstämmer med din en 62368-1

PRODUKTATTRIBUT

Rackhöjd: 3U

Rackbredd: 42HP

Djup: 315.5mm

Antal i förpackningen: 1

Användbar höjd: 112.3mm

Användbar bredd: 219mm

Frontramskonstruktion: Sidbeklädnad; Horisontella skenor

Kylningsalternativ: Nej

Uppfyller: IEC 60297-3-101; IEC 60297-3-102; IEEE 1101.1; IEEE 1101.10; IEEE 1101.11



EMC-skydd: Ja

Yta: Passiverad; Pulverlackerad

Höjd: 132.6mm

Material: Aluminium

Produktfamilj: RatiopacPRO

Produkttyp: Låda

Kapslingsklass: IP20

Statisk belastning: 25kg

Typ: Låda för 19-tums komponenter

Bredd: 235.5mm

Nettovikt: 2.36kg

*The price shown is the per piece price and does not include VAT. Depending on local conditions, packaging and freight charges might not be included. Where these charges should be part of the total price, they are included in the quote. The price given is a non-binding recommended retail price (RRP), which is the nVent list price. The final sales prices of local distributors may vary. Quotations requested or generated on SCHROFF.nVent.com are only valid for commercial customers (B2B). The lead time displayed above is an estimate for this item to be dispatched from an nVent Schroff facility. Transit delivery times are not included in this estimate, as transit time may vary, depending on delivery address, parcel dimensions, and other factors. Cut-outs and modifications placed in non-recommended areas ("collision detected") for configured products may be subject to additional engineering and/or design costs, which may increase initially quoted prices.

YTTERLIGARE PRODUKTINFORMATION

Modifieringar (specialfärger eller storlekar).

Anpassade lösningar (urtag i topplock, basplatta eller sidopaneler).

Monteringsservice från 1 st.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

