


Bolt Expansion Anchor



功能

Heavy duty wedge anchor

For cracked and non-cracked concrete

Fire resistance class R30-R120 for design of anchorages under exposure to fire

Approved for use in seismic design category C1 & C2 (for Drill Bit Diameters 8 mm and greater)

材料: 钢
完成: 电镀锌




技术参数

物料号	订货号	螺纹尺寸 (TS)	长度 (L)	埋置深度	A	钻头直径	认证
SABM10010	400410	M10	90mm	68 mm	10 mm	10mm	VdS, CE, 12-0397
SABM10050	400411	M10	135mm	68 mm	55 mm	10mm	CE, 12-0397, VdS
SABM12015	402170	M12	110mm	80 mm	14 mm	12mm	CE, 12-0397, VdS
SABM12050	401158	M12	150mm	80 mm	54 mm	12mm	VdS, CE, 12-0397
SABM12085	401159	M12	180mm	80 mm	85 mm	12mm	
SABM16025	402171	M16	145mm	97 mm	28 mm	16mm	CE, 12-0397, VdS
SABM20030	402446	M20	167mm	114 mm	32 mm	20mm	VdS, CE, 12-0397
SABM8010	400408	M8	75mm	55 mm	9 mm	8mm	VdS, CE, 12-0397
SABM8050	400409	M8	115mm	55 mm	49 mm	8mm	CE, 12-0397, VdS

Characteristic Axial Loads from ETA-12/0397		
Part Number	Cracked Concrete C20/25	Non-Cracked Concrete C20/25
SABM8010	2.4 kN	3.6 kN
SABM8050	2.4 kN	3.6 kN
SABM10010	4.3 kN	7.6 kN
SABM10050	4.3 kN	7.6 kN
SABM12015	7.6 kN	11.9 kN
SABM12050	7.6 kN	11.9 kN
SABM16025	11.9 kN	16.7 kN
SABM20030	14.3 kN	23.8 kN
SABM8010S6	2.4 kN	4.3 kN
SABM8050S6	2.4 kN	4.3 kN
SABM10010S6	4.3 kN	7.6 kN
SABM10050S6	4.3 kN	7.6 kN

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

