

nVent CADDY Cushion Clamp Insulated Strut Clamp for Pipe/Tube, 22.2mm OD, 15DN



物料号

CCC0087

功能

Fits into open side of strut channel

Plastic cushion is hinged to spread apart for easy installation

Reduces noise and absorbs shock by gripping the pipe/tube firmly

Square neck of carriage bolt prevents over-tightening

Nylon locknut prevents loosening under vibration

FM® Specification Tested (from 3/8" to 4" of Copper Tube Size)



产品属性

订货号: 598891

材料: 钢;聚丙烯

完成: 镀铬酸盐

外径 (OD): 22.2 mm

铜管尺寸: 3/4"

管道尺寸: 1/2"



NB/DN: 15

宽度 (W): 39.7 mm

A: 31.6 mm

B: 48.1 mm

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500

