

nVent CADDY Cushion Clamp Insulated Strut Clamp for Pipe/Tube, 47.6 mm OD, 1 1/2" Pipe, 40 DN



物料号

CCC0187

功能

Fits into open side of strut channel

Plastic cushion is hinged to spread apart for easy installation

Reduces noise and absorbs shock by gripping the pipe/tube firmly

Square neck of carriage bolt prevents over-tightening

Nylon locknut prevents loosening under vibration

FM® Specification Tested (from 3/8" to 4" of Copper Tube Size)



产品属性

订货号: 598903

材料: 钢;聚丙烯

完成: 镀铬酸盐

外径 (OD): 47.6 mm

管道尺寸: 1 1/2"



NB/DN: 40

宽度 (W): 39.7 mm

A: 59 mm

B: 81.5 mm

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

