

Branch Line Restraint Pipe Attachment, 1 1/2" Pipe, 40 DN



物料号

CSBBRP0150EG

功能

Accepts 3/8" or 1/2" (M10 or M12) threaded rod

Quick grip clamp simplifies measuring and cutting of threaded rod

Eliminates need to cut threaded rod to exact dimensions

Works with rough-cut threaded rod and eliminates pipe-side deburring

Can be installed with threaded rod above or below the service pipe

Shear-off head helps ensure correct torque and simplifies inspection



产品属性

订货号: 404479

材料: 钢

完成: 电镀锌

管道尺寸: 1 1/2"

NB/DN: 40

外径 (OD): 48.3 mm



杆尺寸 (RS): 10;12

高度 (H): 88.9 mm

长度 (L): 56.1mm

宽度 (W): 22.2 mm

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221

，按 1 转客户服务

，按 2 转技术支持

欧洲

荷兰：

+31 800-0200135

法国：

+33 800 901 793

欧洲

德国：

800 1890272

其他国家/地区：

+31 13 5835404

亚太地区

上海：

+ 86 21 2412 1618/19

悉尼：

+61 2 9751 8500

