

Branch Line Restraint Structure Attachment to Wood/Concrete, M10, M12 Rod

物料号

CSBBRS2MEG

功能

Swivel barrel nut accepts 3/8" or 1/2" (M10 or M12) threaded rod

Attaches to wood or concrete where cracked concrete approval is not needed



产品属性

订货号: 402240

材料: 钢

完成: 电镀锌

杆尺寸 (RS): 10;12

高度 (H): 28.2 mm

长度 (L): 40.4mm

宽度 (W): 26.9 mm


螺钉直径 (Sc): 1/4"

螺钉长度 (L): 44.5mm

钻头直径: 5mm

Branch line structural attachments are for restraint only and not for the hanging of fire sprinkler piping.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

