

HD Heavy Duty Pipe Clamp, 40–45 mm OD, 1 1/4" Pipe, 32 DN, M8, M10 Rod

物料号

HDI045

功能

Fillet welded connector nut has flats to accommodate spanners

Easy open flange for pipe sizes less than 4"

Category II noise reduction according to DIN EN ISO 3822-1

Compliant for sound insulation design according to DIN 4109

Reaction-to-fire classification is "E" in compliance with DIN EN 13501-1



产品属性

订货号: 577038

材料: 钢;EPDM-SBR 橡胶

完成: 电镀锌

温度: -50 to 110 °C

颜色: 黑色

外径 (OD): 40 - 45 mm

管道尺寸: 1 1/4"

NB/DN: 32


杆尺寸 (RS): M8;M10

宽度 (W): 30 mm
厚度 (T): 2.5 mm
螺钉直径 (Sc): 6 mm
螺钉直径（公制） (Sc): M6
螺钉长度 (L): 30mm
静态负载: 2000N

其他产品详情

Lining is EPDM rubber.

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美	欧洲	欧洲	亚太地区
+1.800.753.9221	荷兰：	德国：	上海：
，按 1 转客户服务	+31 800-0200135	800 1890272	+ 86 21 2412 1618/19
，按 2 转技术支持	法国：	其他国家/地区：	悉尼：
	+33 800 901 793	+31 13 5835404	+61 2 9751 8500

