

# Macrofix Plus NI EZ with Easy Closure, 2" Pipe, DN50, 60.3–63 mm, M10 Rod

## 物料号

**MPZ063**

## 功能

Contains easy closing mechanism

Plastic washers help prevent crushing the CPVC or plastic pipe and assure a floating fit

Flared edges and specially designed welding area help protect CPVC piping

Ideal for installations where space is limited and require services to be ran close to the attachment surface

Suitable for 3/4" - 2" (20 - 50 DN) steel sprinkler pipe

Eliminates the need to seismically brace when drops are kept within 6" (150 mm) of the attachment surface

Combo head bolt works with slotted, hex, or Phillips drivers

Conforms with Manufacturers Standardization Society (MSS) SP-58 (Type 12)



## 产品属性

订货号: 595059

材料: 钢

完成: 电镀锌

管道尺寸: 2" Min



NB/DN: 50


外径 (OD): 60.3 - 63 mm

杆尺寸 (RS): M10

宽度 (W): 30 mm

厚度 (T): 2 mm

静态负载: 1725N



## 警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 [www.nvent.com](http://www.nvent.com) 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

### 北美

+1.800.753.9221

，按 1 转客户服务

，按 2 转技术支持

### 欧洲

荷兰：

+31 800-0200135

法国：

+33 800 901 793

### 欧洲

德国：

800 1890272

其他国家/地区：

+31 13 5835404

### 亚太地区

上海：

+ 86 21 2412 1618/19

悉尼：

+61 2 9751 8500



©2026 nVent. 所有 nVent 标志和徽标均由 nVent Services GmbH 或其附属公司拥有或授权。所有其他商标均为其各自所有者的财产。nVent 保留更改规格的权利，恕不另行通知。

本文档由系统生成。

